MWT27E5

21.3° [541]

6.16

[156

43.74

217 [09] 1

3.0

[77

60 LB. (27KG) CAPACITY

RIGID-MOUNT WASHER-EXTRACTOR

34.45"

875

2

FRONT VIEW

FOUNDATION VIEW

20.09

[510]

F

23.15


[586]

14321


8.16*

[156]

ЗĒ



ANCHORING DETAIL



FLOOR REQUIREMENT MINIMUM 6" RECOMMENDED ◆, ▼, ■

MECHANICAL SPECIFICATIONS


3.04

[77]

Capacity – lb (kg)	60 (27)	
Cylinder Diameter x Depth – in (mm)	30 x 22 (762 x 559)	
Cylinder Volume – cu. ft. (L)	9 (255)	
Door Opening – in (mm)	15.70 (399)	
Machine Dimensions (W x D x H) – in (mm)	34.45 x 51.75 x 56.25 (875 x 1314 x 1429)	
Shipping Dimensions (W x D x H) – in (mm)	40.35 x 54.92 x 60.67 (1025 x 1395 x 1541)	
Motor – HP (kW)	4 (3.0)	
Wash Speed – RPM	38	
Distribution Speed – RPM	65	
Extraction Speed – RPM	485	
Extraction G-Force	100	
Static Weight – lb (kg) ∻	1567 (711)	
Max. Dynamic Load RMS – lb (kg) \diamond	1200 (545)	
Frequency (Hz)	8.07	
Water Pressure (Required) – psi (bar)	10-75 (.68-5.1)	
Water Valve CV Rating	0.92 (3.5)	
Minimum Recommended Distance Between Machines – in (mm)	0 (0)	

SPECIFICATION SHEET

REAR VIEW



LEGEND

2202.10		
С	Cold Water inlet	
D1	Drain 3" (76 mm) ID hose connection	
Е	Main Electrical Connection	
F	Foundation pads, anchor bolt holes .8125" (21 mm) diameter	
G	Hot water inlet for soap chute	
Н	Hot water inlet, .75" (19 mm) GHT	
L1	Standard soap chute	
L2	Liquid supply inlet	

ELECTRICAL SPECIFICATIONS

Voltage	Running Amps	Fuse (Amps)	Circuit Breaker (Amps)
220/3/50	7	FRN15	15
208, 240/1/60	14/12	FRN20	20
208, 240/3/60	8/7	FRN15	15
380/3/50-60	4.5	FRS15	15
415/3/50	4.5	FRS15	15
480/3/60	3.5	FRS15	15

See Fuse and Wire Size manual MAEFUSE1BE for safety information. ▼ See dimensional drawing for complete details.

The floor and/or other support components must have sufficient strength (and rigidity with due consideration for natural or resonant frequency thereof) to withstand the fully loaded weight of the machine including the goods, the water, and any repeated sinusoidal (rotating) forces generated during its operation. Contact the factory for additional machine data for use by a competent soil and/or structural engineer.

 Machine bases made from concrete should either be part of a monolithic pour or should be tied into foundation and not isolated from existing floor.



SPECIFICATION SHEET

Standard Features:

- 3 speeds
- E-P OneTouch[®] controller
- Single-motor inverter drive
- Tall, lifting ribs
- Sealed ball bearings
- High M.A.F. (Mechanical Action Factor)
- Large cylinder perforations
- Fresh-water flushing chemical manifold
- Auto tension V-belt drive
- Three (3) liquid chemical injection ports
- 5-year limited warranty on frame, cylinder & shell



Optional Features:


- Lint trap
- Mounting base



Safe chemical injection



Superior cylinder design



Fits through 3'-0" door



Why Purchase Milnor?

- Larger cylinder volume than most competitive similar sized washer-extractors provides greater productivity. More linen washed per day, or fewer hours required to process. BENEFIT: Saves labor.
- Greater cylinder perforated-area generates better wash quality, better rinsing and better extraction. BENEFIT: Better extraction saves dryer fuel.
- Faster process times reduce fabric wear, promoting *longer linen life*! BENEFIT: Saves linen replacement costs.
- 100-G extract and large cylinder perforated area provide excellent moisture removal. BENEFIT: Better extraction saves dryer fuel.
- Tall perforated ribs provide excellent lift and high drop. BENEFIT: Greater mechanical action (M.A.F.) leads to better wash quality.
- Simple, push-button controls allow for four separate wash formulas. Indicator lights signal when machine is in operation and prompts operator when machine is moving into final wash formula stage. Shortens training time of new employees. BENEFIT: Fewer operator errors.
- Superior product support through local, highly-skilled dealers. BENEFIT: Faster repairs mean less downtime.

Contact Milnor for your local, authorized dealer:

Pellerin Milnor Corporation P.O. Box 400 • Kenner, LA 70063 t: 504-467-9591 • f: 504-468-3094

B22SS16016/D17403 Page 2 of 2